

# CARSON®

## TriView™

### 3x, 5.5x, 8.5x Folding Loupe with Built-in Case

Congratulations on selecting your new TriView™ Folding Loupe! In order to achieve optimum performance, please follow instructions for proper use and care.



# TV-36

#### PRODUCT SPECIFICATION:

Magnification:	3x/5.5x/8.5x
Lens Diameter:	30mm (1.2")
Weight:	0.08 lbs
Dimensions:	4.3 x 1.1 x 1.6"

**FOR BEST RESULTS:** Always use with Carson logo facing up.

#### USING THE MAGNIFIER:

**To achieve 3x magnification,**  
use the top lens.



**To achieve 5.5x magnification,**  
use the top and bottom lenses  
together.



**To achieve 8.5x magnification,**  
use all three lenses stacked.



**Note:** The higher the magnification,  
the closer your eye must be to the  
lens and closer the magnifier must  
be to your viewing surface.

#### CARE:

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

#### Customer Service:

If you experience any difficulties, please contact us and we will be happy to help you.



✉ [info@carson.com](mailto:info@carson.com)



✉ [uksupport@carson.com](mailto:uksupport@carson.com)



✉ [eusupport@carson.com](mailto:eusupport@carson.com)

For warranty information, visit [www.carson.com/warrant](http://www.carson.com/warrant)

[www.carson.com](http://www.carson.com)

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000